


# MultipacPRO Front Handle, One-Piece, Width 10 mm



The front handles can be mounted and provide an easier to mount assembly. The handles can be assembled from the front side.

## CERTIFICATIONS



## FEATURES

Load-carrying capacity 30 kg/pair

Assembly on the front panel

Can be used for the aluminium or sheet metal versions

## SPECIFICATIONS

|                        |                                      |
|------------------------|--------------------------------------|
| <b>Material:</b>       | Aluminum                             |
| <b>Finish:</b>         | Anodized                             |
| <b>Works With:</b>     | Chassis; Front Panels                |
| <b>Product Family:</b> | MultipacPRO; Frame Type Plug-In Unit |
| <b>Product Type:</b>   | Handle                               |

Table 1/1

| Catalog Number | Rack Height | Package Quantity | Handle Type | Color  | Quick Ship |
|----------------|-------------|------------------|-------------|--------|------------|
| 20860-256      | 1U          | 2                | Straight    | Silver | No         |
| 20860-257      | 2U          | 2                | Straight    | Silver | No         |

| Catalog Number | Rack Height | Package Quantity | Handle Type | Color  | Quick Ship |
|----------------|-------------|------------------|-------------|--------|------------|
| 20860-258      | 3U          | 2                | Straight    | Silver | No         |
| 20860-259      | 4U          | 2                | Straight    | Silver | No         |
| 20860-260      | 5U          | 2                | Straight    | Silver | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**