


Novastar Rear Panel With Cable Ducting



Novastar Rear Panel with 3 U or 4 U cable ducting for improved cable management.

CERTIFICATIONS



FEATURES

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Material	Package Quantity	Finish
----------------	-------------	-------	------------	----------	------------------	--------

25230-426	12U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-430	16U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-434	20U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-439	25U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-448	34U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-452	38U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-457	43U	Black Grey	RAL 7021	Steel	1	Powder Coated
25230-461	47U	Black Grey	RAL 7021	Steel	1	Powder Coated
26230-426	12U	Black Grey	RAL 7021	Steel	1	Powder Coated
26230-430	16U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-434	20U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-439	25U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-448	34U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-452	38U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-457	43U	Light Grey	RAL 7035	Steel	1	Powder Coated
26230-461	47U	Light Grey	RAL 7035	Steel	1	Powder Coated
25230-443	29U	Black Grey	RAL 7021	Steel	1	Powder Coated
26230-443	29U	Light Grey	RAL 7035	Steel	1	Powder Coated

Table 2/2

Catalog Number	Type	Certifications	Quick Ship
----------------	------	----------------	------------

25230-426	Rear Panel	RoHS	No
25230-430	Rear Panel	RoHS	No
25230-434	Rear Panel	RoHS	No
25230-439	Rear Panel	RoHS	No
25230-448	Rear Panel	RoHS	No
25230-452	Rear Panel	RoHS	No
25230-457	Rear Panel	RoHS	No
25230-461	Rear Panel	RoHS	No
26230-426	Rear Panel	RoHS	No
26230-430	Rear Panel	RoHS	No
26230-434	Rear Panel	RoHS	No
26230-439	Rear Panel	RoHS	No
26230-448	Rear Panel	RoHS	No
26230-452	Rear Panel	RoHS	No
26230-457	Rear Panel	RoHS	No
26230-461	Rear Panel	RoHS	No
25230-443	Rear Panel		No
26230-443	Rear Panel		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE