


Panhead Screw, Pozidrive

Panhead Screw, Pozidrive.



CERTIFICATIONS



FEATURES

Panhead screw, pozidrive

SPECIFICATIONS

Product Type: Screw **Material:** Steel

Table 1/2						
Catalog Number	Finish	Package Quantity	Thread Size	Product Family	Туре	Works With
21101-314	Nickel Plated	100	M2.5		Panhead Screw	Backplanes, Test Adapters
21101-219	Nickel Plated	100	M2.5	Frame Type Plug-In Unit	Panhead Screw	Backplanes, Test Adapters
21101-069	Nickel Plated	100	M2.5	Frame Type Plug-In Unit	Panhead Screw	Backplanes, Test Adapters
21101-221	Nickel Plated	100	M2.5	Frame Type Plug-In Unit	Panhead Screw	Backplanes, Test Adapters

CatalogNumber	Finish	Package Quantity	Thread Size	Product Family	Туре	Works With
21101-220	Nickel Plated	100	M2.5	Frame Type Plug-In Unit	Panhead Screw	Backplanes, Test Adapters
21102-024	Zinc Plated	100	МЗ		Panhead Screw	
21101-222	Nickel Plated	100	M2.5	Frame Type Plug-In Unit	Panhead Screw	Backplanes, Test Adapters
21100-788	Zinc Plated	100	M5	EuropacPRO	Panhead Screw	Subracks
21120-150	Zinc Plated	100	M5		Coding Block	Cabinet
21100-021	Zinc Plated	50	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21100-650	Zinc Plated	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21100-022	Zinc Plated	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21120-203	Zinc Plated	100	M6		Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
21120-202	Zinc Plated	50	M6		Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP

Table 2/2						
Catalog Number	Thread Type	Certifications	Quick Ship			
21101-314		RoHS	No			
21101-219		RoHS	No			
21101-069		RoHS	No			
21101-221		RoHS	No			
21101-220		RoHS	No			
21102-024	Metric	RoHS	No			
21101-222		RoHS	No			
21100-788		RoHS	No			
21120-150		RoHS	No			
21100-021		RoHS	No			
21100-650		RoHS	No			
21100-022		RoHS	No			
21120-203			No			
21120-202			No			

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE