

PropacPRO Complete Desktop Case, Shielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. The case includes EMC shielding as standard.

CERTIFICATIONS



FEATURES

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Shielded

Ventilation slots in base plate

Rear panel with vent slots

IP 20 in accordance with IEC 60529

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type:	Case
Type:	Case for 19" Components
Product Family:	PropacPRO
EMC Shielding:	Yes

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
----------------	-------------	------------	------------------	--------------------------	----------------	---------------

24576-101	3U	28HP	1	Single Piece	No	IEC 60297-3-101
24576-102	3U	28HP	1	Single Piece	No	IEC 60297-3-101
24576-103	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-104	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-105	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-106	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-107	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-108	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-109	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-110	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-111	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-112	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-113	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-121	6U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-122	6U	84HP	1	Single Piece	No	IEC 60297-3-101

Table 2/2

Catalog Number	Finish	Material	Protection Rating	Quick Ship
24576-101	Passivated, Powder Coated	Aluminum	IP20	No
24576-102	Passivated, Powder Coated	Aluminum	IP20	No
24576-103	Passivated, Powder Coated	Aluminum	IP20	No

Catalog Number	Finish	Material	Protection Rating	Quick Ship
24576-104	Passivated, Powder Coated	Aluminum	IP20	No
24576-105	Passivated, Powder Coated	Aluminum	IP20	No
24576-106	Passivated, Powder Coated	Aluminum	IP20	No
24576-107	Passivated, Powder Coated	Aluminum	IP20	No
24576-108	Passivated, Powder Coated	Aluminum	IP20	No
24576-109	Passivated, Powder Coated	Aluminum	IP20	No
24576-110	Passivated, Powder Coated	Aluminum	IP20	No
24576-111	Passivated, Powder Coated	Aluminum	IP20	No
24576-112	Passivated, Powder Coated	Aluminum	IP20	No
24576-113	Passivated, Powder Coated	Aluminum	IP20	No
24576-121	Passivated, Powder Coated	Aluminum	IP20	No
24576-122	Passivated, Powder Coated	Aluminum	IP20	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE