


PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type:	Case
Type:	Case for 19" Components
EMC Shielding:	No (Retrofittable)
Product Family:	PropacPRO

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
----------------	-------------	------------	------------------	--------------------------	----------------	---------------

24576-001	3U	28HP	1	Single Piece	No	IEC 60297-3-101
24576-002	3U	28HP	1	Single Piece	No	IEC 60297-3-101
24576-003	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-004	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-005	3U	42HP	1	Single Piece	No	IEC 60297-3-101
24576-006	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-007	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-008	3U	63HP	1	Single Piece	No	IEC 60297-3-101
24576-009	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-010	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-011	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-012	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-013	3U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-021	6U	84HP	1	Single Piece	No	IEC 60297-3-101
24576-022	6U	84HP	1	Single Piece	No	IEC 60297-3-101

Table 2/2

Catalog Number	Finish	Material	Protection Rating	Quick Ship
24576-001	Passivated, Powder Coated	Aluminum	IP20	No
24576-002	Passivated, Powder Coated	Aluminum	IP20	No
24576-003	Passivated, Powder Coated	Aluminum	IP20	No

Catalog Number	Finish	Material	Protection Rating	Quick Ship
24576-004	Passivated, Powder Coated	Aluminum	IP20	No
24576-005	Passivated, Powder Coated	Aluminum	IP20	No
24576-006	Passivated, Powder Coated	Aluminum	IP20	No
24576-007	Passivated, Powder Coated	Aluminum	IP20	No
24576-008	Passivated, Powder Coated	Aluminum	IP20	No
24576-009	Passivated, Powder Coated	Aluminum	IP20	No
24576-010	Passivated, Powder Coated	Aluminum	IP20	No
24576-011	Passivated, Powder Coated	Aluminum	IP20	No
24576-012	Passivated, Powder Coated	Aluminum	IP20	No
24576-013	Passivated, Powder Coated	Aluminum	IP20	No
24576-021	Passivated, Powder Coated	Aluminum	IP20	No
24576-022	Passivated, Powder Coated	Aluminum	IP20	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE