


Rear Panel for RatiopacPRO/PropacPRO, Perforated, Retrofit Shielding



The perforated rear panel, Al, 2.5 mm is unshielded. The rear side is conductive.

CERTIFICATIONS



FEATURES

Rear panel, Al, 2.5 mm, front: anodized, rear: conductive; unshielded

Enables mounting on horizontal rails

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Works With:	Cases
Product Family:	RatiopacPRO; RatiopacPRO AIR
Type:	Rear Panel
Product Type:	Side Panel

Table 1/1

Table 1/1				
Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
20848-680	2U	42HP	1	No

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
20848-681	2U	63HP	1	No
20848-633	3U	28HP	1	No
20848-634	3U	42HP	1	No
20848-635	3U	63HP	1	No
20848-636	3U	84HP	1	No
20848-657	4U	42HP	1	No
20848-658	4U	63HP	1	No
20848-659	4U	84HP	1	No
20848-643	6U	84HP	1	No
20848-640	6U	28HP	1	No
20848-641	6U	42HP	1	No
20848-642	6U	63HP	1	No
20848-656	4U	28HP	1	No
20848-679	2U	28HP	1	No
20848-682	2U	84HP	1	No
20848-744	5U	28HP	1	No
20848-745	5U	42HP	1	No
20848-746	5U	63HP	1	No

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
20848-747	5U	84HP	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE