


# Varistar CP Seismic Base Plate, IP55 and EMC, One-Piece

The base plate is solid and covers the base of the cabinet.



## FEATURES

The base plate is solid and covers the base of the cabinet

Is assembled from outside

## SPECIFICATIONS

<b>Product Type:</b>	Cabinet/Rack Base
<b>Finish:</b>	Hot-Dip Galvanized
<b>Protection Rating:</b>	IP55
<b>Material:</b>	Steel

Table 1/1

Catalog Number	Package Quantity	Complies With	Type	Works With	Quick Ship
20630-309	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-310	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-311	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No

Catalog Number	Package Quantity	Complies With	Type	Works With	Quick Ship
20630-312	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-313	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-314	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-315	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No
20630-316	1	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529	Base Plate, Plain	Varistar CP	No

## ADDITIONAL PRODUCT DETAILS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**