

Varistar CP Side Panel With Quick-Release Fastener and Lock

Varistar Side Panels with Quick-Release Fastener without grounding kit.



FEATURES

Steel, 1 mm

Side panel without grounding kit

Safety lock kit included

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Finish	Material
21630-285	24U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-286	24U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-289	29U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-290	29U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-293	33U	2	Black Grey	RAL 7021	Powder Coated	Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Finish	Material
21630-294	33U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-297	38U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-298	38U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-302	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-303	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-304	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-064	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-306	47U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-307	47U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-308	47U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-070	47U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-287	24U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-288	24U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-291	29U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-292	29U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-295	33U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-296	33U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-299	38U	2	Black Grey	RAL 7021	Powder Coated	Steel

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Finish	Material
21630-300	38U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-065	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-066	42U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-071	47U	2	Black Grey	RAL 7021	Powder Coated	Steel
21630-072	47U	2	Black Grey	RAL 7021	Powder Coated	Steel

Table 2/2

Catalog Number	Type	Quick Ship
21630-285	Side Panel, Quick Release	No
21630-286	Side Panel, Quick Release	No
21630-289	Side Panel, Quick Release	No
21630-290	Side Panel, Quick Release	No
21630-293	Side Panel, Quick Release	No
21630-294	Side Panel, Quick Release	No
21630-297	Side Panel, Quick Release	No
21630-298	Side Panel, Quick Release	No
21630-302	Side Panel, Quick Release	No
21630-303	Side Panel, Quick Release	No
21630-304	Side Panel, Quick Release	No
21630-064	Side Panel, Quick Release	No

Catalog Number	Type	Quick Ship
21630-306	Side Panel, Quick Release	No
21630-307	Side Panel, Quick Release	No
21630-308	Side Panel, Quick Release	No
21630-070	Side Panel, Quick Release	No
21630-287	Side Panel, Quick Release	No
21630-288	Side Panel, Quick Release	No
21630-291	Side Panel, Quick Release	No
21630-292	Side Panel, Quick Release	No
21630-295	Side Panel, Quick Release	No
21630-296	Side Panel, Quick Release	No
21630-299	Side Panel, Quick Release	No
21630-300	Side Panel, Quick Release	No
21630-065	Side Panel, Quick Release	No
21630-066	Side Panel, Quick Release	No
21630-071	Side Panel, Quick Release	No
21630-072	Side Panel, Quick Release	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE