


Varistar Slide Rail



Mounts on four 19" slide mounts with 25/100 kg weight capacity.

CERTIFICATIONS



FEATURES

Mounts on four 19" slide mounts

Wide support surface (48 mm)

Can be fitted in 1 U increments (attach and screw into place)

SPECIFICATIONS

Product Type: Slide Rail

Material: Steel

Table 1/1

Catalog Number	Package Quantity	Finish	Works With	Package Unit	Certifications	Quick Ship
23130-096	2	Aluminum-Zinc Plated	Varistar CP	Pair	RoHS	No
23130-097	2	Aluminum-Zinc Plated	Varistar CP	Pair	RoHS	No
23130-098	2	Aluminum-Zinc Plated	Varistar CP	Pair	RoHS	No
23130-099	2	Aluminum-Zinc Plated	Varistar CP	Pair		No
23130-116	2	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-118	2	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-119	2	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-120	2	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-101	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-102	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-103	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-123	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-124	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-125	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No
23130-126	10	Aluminum-Zinc Plated	Varistar CP		RoHS	No

ADDITIONAL PRODUCT DETAILS

For mounting in the cabinet the 19" panel/slide mounts must be fitted front and rear.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE