


nVent CADDY Cat HP J-Hook with Pedestal Clamp



CERTIFICATIONS



FEATURES

Easy installation to pedestals used under raised floors

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A
----------------	----------------	--------------	------	------------------------	-----------------------	------------------------

CAT32HPCD1B	181227	50 mm	2561mm ²	90	60	35
CAT48HPCD1B	181228	75 mm	5974mm ²	200	150	80
CAT64HPCD1B	181229	100 mm	9987mm ²	330	220	140

Table 2/2


Catalog Number	Article Number	Pedestal Size
CAT32HPCD1B	181227	19 mm Square, 22.2 - 28.5 mm Round
CAT48HPCD1B	181228	19 mm Square, 22.2 - 28.5 mm Round
CAT64HPCD1B	181229	19 mm Square, 22.2 - 28.5 mm Round

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

