

Stainless Steel Glazed Doors, DNGS



Electrical components can be viewed while the transparent stainless steel door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: Transparent door fitted with clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking programme.

Material: Frame: 2 mm AISI 304 stainless steel plate, AISI 316L (on request). Viewing area: 4 mm clear safety glass.

Finish: 400 pre-grained stainless steel.

Protection: IP 55, TYPE 12, 13, IK 07.

Mounting requirements: Use hinge kit DNMKS01 if not for replacement of standard door.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 0.08in
Finish: Brushed
Material: Stainless Steel 304

Table 1/1

Catalog Number	Height	Width	Depth	Window Size	Enclosure Material	Product Family
DNGS1408	55.12in	31.5in	0.67in	46.3 x 24.21in	Mild Steel	Free-Standing
DNGS1606	62.99in	23.62in	0.67in	54.17 x 16.34in	Mild Steel	Free-Standing
DNGS1608	62.99in	31.5in	0.67in	54.17 x 24.21in	Mild Steel	Free-Standing
DNGS1610	62.99in	39.37in	0.67in	54.17 x 32.09in	Mild Steel	Free-Standing
DNGS1806	70.87in	23.62in	0.67in	62.05 x 16.34in	Mild Steel	Free-Standing
DNGS1808	70.87in	31.5in	0.67in	62.05 x 24.21in	Mild Steel	Free-Standing
DNGS1810	70.87in	39.37in	0.67in	62.05 x 32.09in	Mild Steel	Free-Standing
DNGS2006	78.74in	23.62in	0.67in	69.92 x 16.34in	Mild Steel	Free-Standing
DNGS2008	78.74in	31.5in	0.67in	69.92 x 24.21in	Mild Steel	Free-Standing
DNGS2010	78.74in	39.37in	0.67in	69.92 x 32.09in	Mild Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE