

Transparent Aluminium Doors, ADA



Components mounted on the enclosure door are protected by the viewing window, but can be easily operated by opening only the viewing window, while the enclosure door can remain closed. The components are protected from the environment and from undesired operations when the viewing window is closed.

FEATURES

Description: Viewing window when used in combination with mounting kit ADAMK. The double-bit 3 mm lock can be replaced by any optional insert or handle. It increases the enclosure depth by 10 mm.

Material: Aluminium and 3 mm acrylic glass.

Finish: Anodised aluminium.

Protection: Complies with IP 54.

Pack quantity: 1 viewing window.

To replace the standard door

Can be used in combination with swing frame, modular chassis or inner door

The double-bit 3 mm lock can be replaced by any optional insert or handle

It increases the enclosures depth by 10 mm (ADA) or 35 mm (ADAB)

Can also be used as a viewing window when used in combination with mounting kit ADAMK/ADABMK

Includes mounting hardware

Number of locks: 1

SPECIFICATIONS

Material: Aluminum

Finish: Mill

Table 1/1

Catalog Number	Height	Width	Depth	Latch Quantity	Window Size	Number of Locking Devices
ADA03030	11.81in	11.81in	1.18in	1	8.9 x 8.9in	1
ADA04030	15.75in	11.81in	1.18in	1	12.83 x 8.9in	1
ADA04040	15.75in	15.75in	1.18in	1	12.83 x 12.83in	1
ADA04060	15.75in	23.62in	1.18in	1	12.83 x 20.71in	1
ADA05030	19.69in	11.81in	1.18in	1	16.77 x 8.9in	1
ADA05040	19.69in	15.75in	1.18in	1	16.77 x 12.83in	1
ADAB06040	23.62in	15.75in	1.18in	2	20.55 x 12.68in	2
ADAB06060	23.62in	23.62in	1.18in	2	20.55 x 20.55in	2
ADAB06080	23.62in	31.5in	1.18in	2	20.55 x 28.43in	2
ADAB07050	27.56in	19.69in	1.18in	2	24.49 x 16.61in	2
ADAB08060	31.5in	23.62in	1.18in	2	28.43 x 20.55in	2
ADAB10080	39.37in	31.5in	1.18in	2	36.3 x 28.43in	2
ADAB12060	47.24in	23.62in	1.18in	2	44.17 x 20.55in	2
ADAB12080	47.24in	31.5in	1.18in	2	44.17 x 28.43in	2

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE