

Wide Mounting Plates, MPW



The extra wide mounting plate offers more mounting space and can be fully equipped before being fitted within the enclosure. It can be fitted from the side of the enclosure since, it is wider than the front of enclosure opening.

FEATURES

Description: Creates an installation surface over the full width of the enclosure. Easy installation by use of sliding profiles MTS from the side. Nominal width equals the enclosure width. When combining enclosures the MPWs can be connected and slid in as one installation surface. Can not be mounted in the rearmost position.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece with mounting accessories.

Mounting requirements: Add sliding profiles MTS. MPW fits in combinable enclosures only.

SPECIFICATIONS

Thickness: 11ga
Finish: Galvanized
Material: Mild Steel

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Quick Ship |
|----------------|----------------|---------|---------|--------|--------------------|------------|
| MPW1808 | MPW1808 | 70.87in | 31.5in | 0.98in | Mild Steel | No |
| MPW1810 | MPW1810 | 70.87in | 39.37in | 0.98in | Mild Steel | No |
| MPW1812 | MPW1812 | 70.87in | 47.24in | 0.98in | Mild Steel | No |
| MPW1816 | MPW1816 | 70.87in | 63in | 0.98in | Mild Steel | No |
| MPW2008 | MPW2008 | 78.74in | 31.5in | 0.98in | Mild Steel | No |
| MPW2010 | MPW2010 | 78.74in | 39.37in | 0.98in | Mild Steel | No |
| MPW2012 | MPW2012 | 78.74in | 47.24in | 0.98in | Mild Steel | No |
| MPW2016 | MPW2016 | 78.74in | 63in | 0.98in | Mild Steel | No |
| MPW1805 | MPW1805 | 70.87in | 19.69in | 0.98in | Mild Steel | No |
| MPW1806 | MPW1806 | 70.87in | 23.62in | 0.98in | Mild Steel | No |
| MPW2005 | MPW2005 | 78.74in | 19.69in | 0.98in | Mild Steel | No |
| MPW2006 | MPW2006 | 78.74in | 23.62in | 0.98in | Mild Steel | No |

ADDITIONAL PRODUCT DETAILS

* 1600 mm wide mounting plates are supplied as two 800 mm wide mounting plates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE