


Front Panel, Unshielded, Bottom Hinged

Power Utilities

Unshielded front panel bottom hinged.



CERTIFICATIONS



FEATURES

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20838-271	3 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20838-272	3 U	63 HP	1	Hinged, Bottom	Anodized	Conductive
20838-273	3 U	84 HP	1	Hinged, Bottom	Anodized	Conductive

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
20838-274	6 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20838-275	6 U	63 HP	1	Hinged, Bottom	Anodized	Conductive
20838-276	6 U	84 HP	1	Hinged, Bottom	Anodized	Conductive
20838-277	4 U	42 HP	1	Hinged, Bottom	Anodized	Conductive
20838-278	4 U	63 HP	1	Hinged, Bottom	Anodized	Conductive
20838-279	4 U	84 HP	1	Hinged, Bottom	Anodized	Conductive
20838-280	3 U	28 HP	1	Hinged, Bottom	Anodized	Conductive

Table 2/2						
Catalog Number	Treated Edges	Complies With	EMC Shielding	Material	Product Type	Type
20838-271	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-272	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-273	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-274	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-275	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-276	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-277	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Material	Product Type	Type
20838-278	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-279	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle
20838-280	No	IEC 60297-3-101, IEEE 1101.1/10	No	Aluminum	Front Panel	Front Panel without Handle

ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position (> 135°).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE