

Novastar Cabinet With Glazed Door and Rear Panel

Power Utilities



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



FEATURES

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Frame Color	Frame Color Code	Cladding Material	Cladding Color	Cladding Color Code
----------------	-------------	-------------	------------------	-------------------	----------------	---------------------

15230-019	12 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
16230-019	12 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
15230-020	16 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
16230-020	16 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
15230-021	20 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
16230-021	20 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
15230-022	38 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
15230-023	38 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
16230-022	38 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
16230-023	38 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
15230-024	43 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
15230-025	43 U	Black Grey	RAL 7021	Steel	Black Grey	RAL 7021
16230-024	43 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035
16230-025	43 U	Black Grey	RAL 7021	Steel	Light Grey	RAL 7035

Table 2/2				
Catalog Number	Complies With	Frame Material	Product Type	Protection Rating
15230-019	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-019	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
15230-020	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-020	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20

Catalog Number	Complies With	Frame Material	Product Type	Protection Rating
15230-021	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-021	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
15230-022	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
15230-023	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-022	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-023	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
15230-024	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
15230-025	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-024	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20
16230-025	IEC 60529, IEC 60297-3-100	Aluminum	Cabinet	IP20

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE