

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Power Utilities

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Finish	Locking Type
21630-171	47 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-210	24 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-211	29 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-212	33 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-213	38 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-214	42 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-215	47 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-216	24 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking

CatalogNumber	Rack Height	Color	Color Code	Complies With	Finish	Locking Type
21630-217	29 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-218	33 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-219	38 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking
21630-220	42 U	Black Grey	RAL 7021	IEC 61587-1	Powder Coated	3-Point Locking

Table 2/2					
Catalog Number	Material	Product Type	Protection Rating	Type	Works With
21630-171	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-210	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-211	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-212	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-213	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-214	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-215	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-216	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-217	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-218	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-219	Steel	Cabinet Door	IP55	Steel Door	Varistar CP
21630-220	Steel	Cabinet Door	IP55	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE