

On Demand Stock Panels: NGC-40



nVent RAYCHEM NGC-40 On Demand Stock Panels offer rapid delivery of optimized best-in-class standard panel configurations for customer projects. Panels are built with quality components including premium RAYCHEM controllers for use in hazardous and nonhazardous areas. Many configurations have C1D2 circuit breakers and Type 4X stainless steel enclosures.

FEATURES

Improve efficiency and reduce lead times by using standardized EHT controller & panel designs

Broad selection of configurations available immediately with best-in-class advanced control options

Consistent design with time-tested quality for your project

SPECIFICATIONS

Table 1/2								
Catalog Number	Item Name	Circuit Breaker Voltage Rating	Main Circuit Breaker Current Rating	Touchscreen Included	Height	Width		
101723-001	NGC-40-F-4-H- 480-N-110			No	37 in	31 in		
101723-003	NGC-40-F-4X-H- 20(1P)30A-277- 80-N-0	277 V	70 A	No	60 in	36 in		
101723-002	NGC-40-F-4X-H- 10(1P)30A-277- 50-N-0	277 V	50 A	No	60 in	36 in		
101723-005	NGC-40-F-4X-H- 40(1P)30A-277- 175-N-0	277 V	175 A	No	72 in	48 in		
101723-004	NGC-40-F-4X-H- 30(1P)30A-277- 125-N-0	277 V	125 A	No	72 in	48 in		

Table 2/2								
Catalog Number	Item Name	Depth	Control Relay Type	Voltage Rating				
101723-001	NGC-40-F-4-H-480-N- 110	12 in	Solid State	277 – 480 V				
101723-003	NGC-40-F-4X-H- 20(1P)30A-277-80-N-0	16 in	Solid State	277 – 480 V				
101723-002	NGC-40-F-4X-H- 10(1P)30A-277-50-N-0	16 in	Solid State	277 – 480 V				
101723-005	NGC-40-F-4X-H- 40(1P)30A-277-175-N- 0	24 in	Solid State	277 – 480 V				
101723-004	NGC-40-F-4X-H- 30(1P)30A-277-125-N- 0	24 in	Solid State	277 – 480 V				

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa Tel +32.16.213.511

Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com