

Modular Jumper Cable, Metal Connectors

nVent RAYCHEM TraceTek TT-MJC-XX is a range of jumper cables, with metal connectors, available in various fixed lengths.

FEATURES

Simple and fast to install, modular

Easy to design

SPECIFICATIONS

Core Quantity:	4
Conductor Size:	18 AWG
Core Identification:	Color
Conductor Material:	Copper
Outer Sheath Material:	ECTFE
Insulation Material:	Fluorinated Ethylene Propylene (FEP)
Connector Material:	Metal

Table 1/1

Catalog Number	Item Name	Outer Diameter	Length	Color
013247-000	TT-MJC-1M/3FT-MC	0.165 in	3 ft	Clear Jacket
057111-000	TT-MJC-15M/50FT-MC	0.165 in	50 ft	Clear Jacket
078783-000	TT-MJC-3M/10FT-MC	0.165 in	10 ft	Clear Jacket
169643-000	TT-MJC-7M/25FT-MC	0.165 in	25 ft	Clear Jacket
935637-000	TT-MJC-30M/100FT-MC	0.165 in	100 ft	Clear Jacket
664356-000	TT-MJC-30M/100FT-MC-BLK	0.17 in	100 ft	Black
678452-000	TT-MJC-15M/50FT-MC-BLK	0.17 in	50 ft	Black

Catalog Number	Item Name	Outer Diameter	Length	Color
693994-000	TT-MJC-7.5M/25FT-MC-BLK	0.17 in	25 ft	Black
709898-000	TT-MJC-3M/10FT-MC-BLK	0.17 in	10 ft	Black
726164-000	TT-MJC-1M/3FT-MC-BLK	0.17 in	3 ft	Black

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT