


# EuropacPRO Mounting Plate for Use With Cover Plate

## Power Utilities



Mounting plate for use with cover plates for installation and fixing of heavy components. Full width mounting plates (as wide as the subrack or the system case) are fixed to the side panels. The partial width mounting plates are fixed to the side panel and horizontal rail by means of an assembly strip.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

## CERTIFICATIONS



## FEATURES

For installation and fixing of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

A guide rail can be fitted in first and last slot position

In addition to the mounting plate EMC cover plates can also be fitted to the subrack

Guide rails type 4.4 and "strengthened" cannot be used

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Width | Package Quantity | Depth    | Material | Product Family | Product Type   |
|----------------|------------|------------------|----------|----------|----------------|----------------|
| 34563-019      | 63 HP      | 1                | 172.5 mm | Aluminum | EuropacPRO     | Mounting Plate |

| CatalogNumber | Rack Width | Package Quantity | Depth    | Material | Product Family | Product Type   |
|---------------|------------|------------------|----------|----------|----------------|----------------|
| 34563-001     | 28 HP      | 1                | 112.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-003     | 63 HP      | 1                | 112.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-044     | 84 HP      | 1                | 412.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-042     | 84 HP      | 1                | 352.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-009     | 28 HP      | 1                | 172.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-002     | 42 HP      | 1                | 112.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-028     | 84 HP      | 1                | 292.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-026     | 84 HP      | 1                | 232.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-014     | 42 HP      | 1                | 172.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-024     | 84 HP      | 1                | 172.5 mm | Aluminum | EuropacPRO     | Mounting Plate |
| 34563-004     | 84 HP      | 1                | 112.5 mm | Aluminum | EuropacPRO     | Mounting Plate |

| Table 2/2      |           |            |                |
|----------------|-----------|------------|----------------|
| Catalog Number | Width     | Works With | Certifications |
| 34563-019      | 324.67 mm | Subracks   | RoHS           |
| 34563-001      | 146.88 mm | Subracks   | RoHS           |
| 34563-003      | 324.67 mm | Subracks   | RoHS           |
| 34563-044      | 431.35 mm | Subracks   |                |
| 34563-042      | 431.35 mm | Subracks   |                |
| 34563-009      | 146.88 mm | Subracks   | RoHS           |

| Catalog Number | Width     | Works With | Certifications |
|----------------|-----------|------------|----------------|
| 34563-002      | 217.99 mm | Subracks   | RoHS           |
| 34563-028      | 431.35 mm | Subracks   |                |
| 34563-026      | 431.35 mm | Subracks   |                |
| 34563-014      | 217.99 mm | Subracks   | RoHS           |
| 34563-024      | 431.35 mm | Subracks   | RoHS           |
| 34563-004      | 431.35 mm | Subracks   | RoHS           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE