

RIM2-E Eave Panel



nVent RAYCHEM RIM2-E panels are designed to mount on the roof eave and minimize the formation of icicles and ice dams during the winter season. RIM2-E panels embed 2 runs of energy efficient self-regulating heating cable in a specially designed base that directs most of the heat to the top surface for maximum efficiency. The base and heating cable are covered with cover panel which transfers heat along the continuous edge of the roof. The cover panels are available in variety of colors to match the roof material.

FEATURES

- Prevents ice dam and icicle problems in eaves and valleys, avoids consequential roof damage
- An aesthetically attractive solution, with no visible cables, various colors and finishes
- Simple to install and operate
- Energy efficient, self-regulating heating cable plus advanced UL and CSA Certified control systems
- Reliable during long life: 20 year product warranty available
- Maintenance free

SPECIFICATIONS

- Heating Capacity:** 16 W/ft
- Cable Type:** Self-Regulating

Table 1/1		
Catalog Number	Nominal Voltage	Color
F6237-AL-01-1	120 V	Slate Gray
F6237-AL-01-2	240 V	Slate Gray
F6237-AL-02-1	120 V	Stone White
F6237-AL-02-2	240 V	Stone White

Catalog Number	Nominal Voltage	Color
F6237-AL-03-1	120 V	Bone White
F6237-AL-03-2	240 V	Bone White
F6237-AL-04-1	120 V	Almond
F6237-AL-04-2	240 V	Almond
F6237-AL-05-1	120 V	Sandstone
F6237-AL-05-2	240 V	Sandstone
F6237-AL-06-1	120 V	Sierra Tan
F6237-AL-06-2	240 V	Sierra Tan
F6237-AL-07-1	120 V	Teal
F6237-AL-07-2	240 V	Teal
F6237-AL-08-1	120 V	Regal Blue
F6237-AL-08-2	240 V	Regal Blue
F6237-AL-09-1	120 V	Sky Blue
F6237-AL-09-2	240 V	Sky Blue
F6237-AL-10-1	120 V	Sherwood Green
F6237-AL-10-2	240 V	Sherwood Green
F6237-AL-11-1	120 V	Hartford Green
F6237-AL-11-2	240 V	Hartford Green

Catalog Number	Nominal Voltage	Color
F6237-AL-12-1	120 V	Hemlock Green
F6237-AL-12-2	240 V	Hemlock Green
F6237-AL-13-1	120 V	Patina Green
F6237-AL-13-2	240 V	Patina Green
F6237-AL-14-1	120 V	Dark Ivy
F6237-AL-14-2	240 V	Dark Ivy
F6237-AL-15-1	120 V	Brandy Wine
F6237-AL-15-2	240 V	Brandy Wine
F6237-AL-16-1	120 V	Regal Red
F6237-AL-16-2	240 V	Regal Red
F6237-AL-17-1	120 V	Colonial Red
F6237-AL-17-2	240 V	Colonial Red
F6237-AL-18-1	120 V	Terra Cotta
F6237-AL-18-2	240 V	Terra Cotta
F6237-AL-19-1	120 V	Dark Bronze
F6237-AL-19-2	240 V	Dark Bronze
F6237-AL-20-1	120 V	Extra Dark Bronze
F6237-AL-20-2	240 V	Extra Dark Bronze

Catalog Number	Nominal Voltage	Color
F6237-AL-21-1	120 V	Mansard Brown
F6237-AL-21-2	240 V	Mansard Brown
F6237-AL-22-1	120 V	Medium Bronze
F6237-AL-22-2	240 V	Medium Bronze
F6237-AL-23-1	120 V	Matte Black
F6237-AL-23-2	240 V	Matte Black
F6237-AL-24-1	120 V	Classic Copper
F6237-AL-24-2	240 V	Classic Copper
F6237-AL-25-1	120 V	Silver Metallic
F6237-AL-25-2	240 V	Silver Metallic
F6237-AL-26-1	120 V	Champagne Metallic
F6237-AL-26-2	240 V	Champagne Metallic
F6237-AL-27-1	120 V	Cityscape
F6237-AL-27-2	240 V	Cityscape
F6237-AL-28-1	120 V	Charcoal Gray
F6237-AL-28-2	240 V	Charcoal Gray
F6237-AL-29-1	120 V	Tropical Patina
F6237-AL-29-2	240 V	Tropical Patina

Catalog Number	Nominal Voltage	Color
F6237-AL-30-1	120 V	Electric Blue
F6237-AL-30-2	240 V	Electric Blue
F6237-AL-31-1	120 V	Award Blue
F6237-AL-31-2	240 V	Award Blue
F6237-AL-32-1	120 V	Granite Green
F6237-AL-32-2	240 V	Granite Green
F6237-CU-70-1	120 V	Copper
F6237-CU-70-2	240 V	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT