

# 19" Fan Unit Housing, 1 U



Create your 19" fan trays from individual parts (assembled within 10 working days).

## CERTIFICATIONS



## FEATURES

Fan enclosure (without front panel) to accommodate fans

Cover/base plate, St, 1 mm, finish AlZn, with perforation

## SPECIFICATIONS

Table 1/1

| Catalog Number | Finish               | Material | Package Quantity | Quick Ship |
|----------------|----------------------|----------|------------------|------------|
| 20713-219      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-216      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-215      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-217      | Aluminum-Zinc Plated | Steel    | 1                | No         |

| Catalog Number | Finish               | Material | Package Quantity | Quick Ship |
|----------------|----------------------|----------|------------------|------------|
| 20713-214      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-218      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-213      | Aluminum-Zinc Plated | Steel    | 1                | No         |
| 20713-212      | Aluminum-Zinc Plated | Steel    | 1                | No         |

## ADDITIONAL PRODUCT DETAILS

Versions for 115 V or with switch available on request.

Unused fan mounting positions are covered with foam material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**