


Air Baffle, U-Front Panel, Refrofit Shielding, Textile



The air baffle with U-shaped front panel covers an empty slot to eliminate an air flow exit. The U-shaped front panel accepts a textile EMC gasket.

CERTIFICATIONS



FEATURES

air baffle eliminates air leaks in empty slots

Cover is pushed into the guide rail

SPECIFICATIONS

| | |
|------------------------|---|
| Product Type: | Air Baffle |
| Material: | Aluminum |
| Finish: | Anodized; Passivated |
| Product Family: | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac |
| Type: | With Front Panel |

Table 1/1

| Catalog Number | Rack Height | Package Quantity | EMC Shielding | Rack Width | Works With | Quick Ship |
|----------------|-------------|------------------|--------------------|------------|-----------------|------------|
| 20848-728 | 3U | 1 | No (Retrofittable) | 4HP | Subracks, Cases | No |

| CatalogNumber | Rack Height | Package Quantity | EMC Shielding | Rack Width | Works With | Quick Ship |
|---------------|-------------|------------------|--------------------|------------|-----------------|------------|
| 20848-729 | 3U | 1 | No (Retrofittable) | 4HP | Subracks, Cases | No |
| 20848-736 | 6U | 1 | No (Retrofittable) | 4HP | Subracks, Cases | No |
| 20848-737 | 6U | 1 | No (Retrofittable) | 4HP | Subracks, Cases | No |

ADDITIONAL PRODUCT DETAILS

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE