

# **ATCA Front Panel Kit With Spring Loading**



AdvancedTCA front panel for spring-loaded IEA handle (plunger or lever style) with die-cast end piece in Al-Profile or stainles material.

#### **CERTIFICATIONS**



# **FEATURES**

Front panel (reinforced with diecast endpiece)

ATCA IEA handle with spring loading

EMC textile gasket and fixing material

# **SPECIFICATIONS**


**Rack Width:** 6HP **Rack Height:** 8U

Accessory Type: Front panel Product Type: Front Panel

| Table 1/1         |          |            |                     |              |             |            |  |  |  |
|-------------------|----------|------------|---------------------|--------------|-------------|------------|--|--|--|
| Catalog<br>Number | Material | Finish     | Package<br>Quantity | Front Finish | Rear Finish | Quick Ship |  |  |  |
| 20818-170         | Aluminum | Passivated | 1                   | Raw          | Raw         | No         |  |  |  |
| 20818-169         | Aluminum | Passivated | 1                   | Raw          | Raw         | No         |  |  |  |

| CatalogNumber | Material        | Finish | Package<br>Quantity | Front Finish | Rear Finish | Quick Ship |
|---------------|-----------------|--------|---------------------|--------------|-------------|------------|
| 20818-161     | Stainless Steel |        | 1                   | Raw          | Raw         | No         |
| 20818-160     | Stainless Steel |        | 1                   | Raw          | Raw         | No         |

# **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE