

CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



CERTIFICATIONS



FEATURES

The front panel is bolted to the front frame of the enclosure

SPECIFICATIONS

Material:AluminumFinish:AnodizedAccessory Type:Front panelProduct Type:Front Panel

Table 1/2						
Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
30823-209	2U	42HP	1	Anodized	Anodized	No
30823-254	3U	28HP	1	Anodized	Anodized	No
30823-257	3U	42HP	1	Anodized	Anodized	No

CatalogNumber	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
30823-215	2U	84HP	1	Anodized	Anodized	No
30823-269	4U	42HP	1	Anodized	Anodized	No
30823-224	3U	63HP	1	Anodized	Anodized	No
30823-260	3U	84HP	1	Anodized	Anodized	No
30823-227	4U	63HP	1	Anodized	Anodized	No
30823-272	4U	84HP	1	Anodized	Anodized	No
30823-230	6U	63HP	1	Anodized	Anodized	No
30823-284	6U	84HP	1	Anodized	Anodized	No

Table 2/2					
Catalog Number	EMC Shielding	Quick Ship			
30823-209	No	No			
30823-254	No	No			
30823-257	No	No			
30823-215	No	No			
30823-269	No	No			
30823-224	No	No			
30823-260	No	No			
30823-227	No	No			
30823-272	No	No			

Catalog Number	EMC Shielding	Quick Ship
30823-230	No	No
30823-284	No	No

ADDITIONAL PRODUCT DETAILS

Assembly Kit to fix one rear and one front panel is included with the case.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE