

# CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



## CERTIFICATIONS



## FEATURES

The front panel is bolted to the front frame of the enclosure

## SPECIFICATIONS

<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized
<b>Accessory Type:</b>	Front panel
<b>Product Type:</b>	Front Panel

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
30823-209	2U	42HP	1	Anodized	Anodized	No
30823-215	2U	84HP	1	Anodized	Anodized	No
30823-254	3U	28HP	1	Anodized	Anodized	No

CatalogNumber	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
30823-257	3U	42HP	1	Anodized	Anodized	No
30823-224	3U	63HP	1	Anodized	Anodized	No
30823-260	3U	84HP	1	Anodized	Anodized	No
30823-269	4U	42HP	1	Anodized	Anodized	No
30823-227	4U	63HP	1	Anodized	Anodized	No
30823-272	4U	84HP	1	Anodized	Anodized	No
30823-230	6U	63HP	1	Anodized	Anodized	No
30823-284	6U	84HP	1	Anodized	Anodized	No

Table 2/2

Catalog Number	EMC Shielding	Quick Ship
30823-209	No	No
30823-215	No	No
30823-254	No	No
30823-257	No	No
30823-224	No	No
30823-260	No	No
30823-269	No	No
30823-227	No	No
30823-272	No	No

Catalog Number	EMC Shielding	Quick Ship
30823-230	No	No
30823-284	No	No

## ADDITIONAL PRODUCT DETAILS

Assembly Kit to fix one rear and one front panel is included with the case.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**