



Aisle Containment Automatic Top Cover, 1200W 600D, RAL 7021

CATALOG NUMBER

21130-592



Top cover that can be automatically opened in case of an event on site.

CERTIFICATIONS



FEATURES

Automatic containment top covers open automatically in the event of fire so that the facility sprinkler systems can put out the fire. In normal operation, the top covers are kept closed by electromagnets and open when the floating contact of the fire detection system is opened

Suitable for an aisle width of 1200 mm

Top cover with safety glass, 7 mm

With the universal top cover profile, the aisle height can be increased by 84 mm; please order separately

The top cover can be removed from the inside. When opened, the top cover provides access to lighting and sprinkler systems above the containment system for maintenance work

Please order the control unit, which can be used to control up to 12 automatic top covers, separately

A 24 VDC power supply unit is required to operate the system. Please order separately

PRODUCT ATTRIBUTES

Package Quantity: 1
Color: Black Grey
Color Code: RAL 7021
Finish: Powder Coated
Material: Steel; Glass
Product Type: Cover
Type: Aisle Top Cover, Automatic
Works With: Aisle Containment

ADDITIONAL PRODUCT DETAILS

Please order the control unit, which can be used to control up to 12 automatic top covers, separately.

A 24 VDC power supply unit is required to operate the system. Please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE