


# Universal Connection Terminal, WO60



Terminals for connecting round conductors on to flat busbars 1,5 mm<sup>2</sup> to 120 mm<sup>2</sup>.

## INDUSTRY STANDARDS

---

UL

CSA

GL

DNV-GL

## FEATURES

---

Description: Universal conductor terminal with integrated holding spring, a captive clamping screw, and open terminal space.

Rated voltage: 690 V

Approvals: CSA, UL, GL, DNV-GL

Indication of nominal cross-section and tightening torque is noted on the terminal

Can be used with cover cap 01590

Universal conductor terminal with integrated holding spring, a captive clamping screw, and open terminal space

Rated voltage: 690 V

## SPECIFICATIONS

**Material:** Mild Steel

**Finish:** Plated

Table 1/1

| Catalog Number | Height | Width  | Depth | Connection Type          | Max Current | Package Quantity |
|----------------|--------|--------|-------|--------------------------|-------------|------------------|
| 01068          | 15mm   | 17mm   | 21mm  | 16 - 120 mm <sup>2</sup> | 440A        | 25               |
| 01284          | 7.5mm  | 7.5mm  | 21mm  | 1.5 - 16 mm <sup>2</sup> | 180A        | 100              |
| 01285          | 11mm   | 10.5mm | 21mm  | 4 - 35 mm <sup>2</sup>   | 270A        | 50               |
| 01287          | 14mm   | 14mm   | 21mm  | 16 - 70 mm <sup>2</sup>  | 400A        | 25               |
| 01289          | 7.5mm  | 7.5mm  | 21mm  | 1.5 - 16 mm <sup>2</sup> | 180A        | 100              |
| 01203          | 15mm   | 17mm   | 21mm  | 16 - 120 mm <sup>2</sup> | 440A        | 25               |
| 01290          | 11mm   | 10.5mm | 21mm  | 4 - 35 mm <sup>2</sup>   | 270A        | 50               |
| 01292          | 14mm   | 14mm   | 21mm  | 16 - 70 mm <sup>2</sup>  | 400A        | 25               |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**