

# Interscale Desktop Case, Non-Perforated



Flexible desktop case with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

#### **CERTIFICATIONS**



#### **FEATURES**

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases upon request

## **SPECIFICATIONS**

Material: Aluminum; Steel

Type: Desktop
Product Family: Interscale
Protection Rating: IP30
Color Code: RAL 7016

**Product Type:** Small Form Factor Case

| Table 1/1      |                  |         |       |        |            |  |  |  |
|----------------|------------------|---------|-------|--------|------------|--|--|--|
| Catalog Number | Package Quantity | Cooling | Color | Finish | Quick Ship |  |  |  |

| 14820-133 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
|-----------|---|----------------|-----------------|---|----|
| 14820-134 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-154 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-254 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-155 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-175 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-195 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-197 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-255 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-275 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-295 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-297 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-375 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-395 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |
| 14820-397 | 1 | Non-Perforated | Anthracite Grey | Aluminum-Zinc<br>Plated, Powder<br>Coated | No |

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE