


Mounting Plate for 19" Case and Subrack



Mounting plate for heavy components or proprietary electronic assemblies. Suitable for RatiopacPRO/-AIR, CompacPRO and EuropacPRO.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

CERTIFICATIONS



FEATURES

For assembly of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

Mounting plate, partial width: The partial width mounting plate fixed to the side panel by means of an assembly strip

The chassis plate can't be combined with EMC top- / bottom covers

SPECIFICATIONS

Material:AluminumProduct Type:Mounting PlateWorks With:Subracks

Table 1/1								
Catalog Number	Rack Width	Package Quantity	Product Family	Certifications	Quick Ship			
34562-745	28HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No			
34562-749	28HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No			

Catalog Number	Rack Width	Package Quantity	Product Family	Certifications	Quick Ship
34562-746	42HP	1	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-753	28HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-747	63HP	1	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-757	28HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-750	42HP	1	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	RoHS	No
34562-748	84HP	1	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-754	42HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-751	63HP	1	EuropacPRO, RatiopacPRO, CompacPRO, PropacPRO	RoHS	No
34562-758	42HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-752	84HP	1	EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO	RoHS	No
34562-755	63HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-759	63HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-756	84HP	1	EuropacPRO, RatiopacPRO, CompacPRO	RoHS	No

Catalog Number	Rack Width	Package Quantity	Product Family	Certifications	Quick Ship
34562-760	84HP	1	EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO	RoHS	No
34562-870	84HP	1	EuropacPRO		No
34562-871	84HP	1	EuropacPRO		No

ADDITIONAL PRODUCT DETAILS

Please order assembly kit for mounting plate separately.

Other versions on request.

Fixing strips required for partial width, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE