


Novastar Perforated Steel Door



Perforated doors allow 60 % ventilation thus allowing better passive cooling. Novastar perforated doors come with 180° opening angle and aesthetic looks.

CERTIFICATIONS



FEATURES

Can be mounted at front and rear

Perforated (60 % ventilation opening)

Opening angle 180°

Lock with key (2233X)

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Finish	Type
25230-081	6U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-082	9U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Finish	Type
25230-083	12U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-084	16U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-085	20U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-086	25U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-087	34U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-088	38U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-089	43U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-090	47U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
25230-091	29U	1	Black Grey	RAL 7021	Powder Coated	Steel Door, Perforated
26230-081	6U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-082	9U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-083	12U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-084	16U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-085	20U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-086	25U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-087	34U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-088	38U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-089	43U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Finish	Type
26230-090	47U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated
26230-091	29U	1	Light Grey	RAL 7035	Powder Coated	Steel Door, Perforated

Table 2/2

Catalog Number	Quick Ship
25230-081	No
25230-082	No
25230-083	No
25230-084	No
25230-085	No
25230-086	No
25230-087	No
25230-088	No
25230-089	No
25230-090	No
25230-091	No
26230-081	No
26230-082	No
26230-083	No
26230-084	No

Catalog Number	Quick Ship
26230-085	No
26230-086	No
26230-087	No
26230-088	No
26230-089	No
26230-090	No
26230-091	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE