


Varistar 19" Panel/Slide Mount



Slide mounts with adjustable increments.

CERTIFICATIONS



FEATURES

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

Assembly in 600 mm wide cabinets directly on the frame

For 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary

Dimensions are engraved in U increments (1 ... 52 U)

Made of Steel, 2 mm thick

Subsequent assembly possible

SPECIFICATIONS

Product Type: Slide Mount

Material: Steel

Table 1/2

Catalog Number	Rack Height	Finish	Package Quantity	Color	Color Code	Package Unit
23130-011	24U	Powder Coated	2	Black Grey	RAL 7021	Pair
23130-012	29U	Powder Coated	2	Black Grey	RAL 7021	Pair
23130-013	33U	Powder Coated	2	Black Grey	RAL 7021	
23130-014	38U	Powder Coated	2	Black Grey	RAL 7021	Pair
23130-015	42U	Powder Coated	2	Black Grey	RAL 7021	Pair
23130-016	47U	Powder Coated	2	Black Grey	RAL 7021	Pair
23130-017	8U	Powder Coated	2	Black Grey	RAL 7021	
23130-018	12U	Powder Coated	2	Black Grey	RAL 7021	
23130-019	16U	Powder Coated	2	Black Grey	RAL 7021	
23130-020	20U	Powder Coated	2	Black Grey	RAL 7021	
23130-021	24U	Powder Coated	2	Light Grey	RAL 7035	
23130-022	29U	Powder Coated	2	Light Grey	RAL 7035	
23130-023	33U	Powder Coated	2	Light Grey	RAL 7035	

CatalogNumber	Rack Height	Finish	Package Quantity	Color	Color Code	Package Unit
23130-024	38U	Powder Coated	2	Light Grey	RAL 7035	
23130-025	42U	Powder Coated	2	Light Grey	RAL 7035	
23130-026	47U	Powder Coated	2	Light Grey	RAL 7035	
23130-027	8U	Powder Coated	2	Light Grey	RAL 7035	
23130-028	12U	Powder Coated	2	Light Grey	RAL 7035	
23130-029	16U	Powder Coated	2	Light Grey	RAL 7035	
23130-030	20U	Powder Coated	2	Light Grey	RAL 7035	
23130-031	24U	Aluminum-Zinc Plated	2			Pair
23130-032	29U	Aluminum-Zinc Plated	2			Pair
23130-033	33U	Aluminum-Zinc Plated	2			
23130-034	38U	Aluminum-Zinc Plated	2			Pair
23130-035	42U	Aluminum-Zinc Plated	2			Pair
23130-036	47U	Aluminum-Zinc Plated	2			Pair
23130-037	8U	Aluminum-Zinc Plated	2			
23130-038	12U	Aluminum-Zinc Plated	2			
23130-039	16U	Aluminum-Zinc Plated	2			
23130-040	20U	Aluminum-Zinc Plated	2			
23130-570	52U	Powder Coated	2	Black Grey	RAL 7021	

CatalogNumber	Rack Height	Finish	Package Quantity	Color	Color Code	Package Unit
23130-588	52U	Aluminum-Zinc Plated	2	Black Grey	RAL 7021	

Table 2/2

Catalog Number	Quick Ship
23130-011	No
23130-012	No
23130-013	No
23130-014	No
23130-015	No
23130-016	No
23130-017	No
23130-018	No
23130-019	No
23130-020	No
23130-021	No
23130-022	No
23130-023	No
23130-024	No
23130-025	No
23130-026	No

Catalog Number	Quick Ship
23130-027	No
23130-028	No
23130-029	No
23130-030	No
23130-031	No
23130-032	No
23130-033	No
23130-034	No
23130-035	No
23130-036	No
23130-037	No
23130-038	No
23130-039	No
23130-040	No
23130-570	No
23130-588	No

ADDITIONAL PRODUCT DETAILS

For 19" partial-height mounting depth members are necessary.

Metric panel/slide mounts available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE