


# Insertor/Extractor Handle Type XL; 10 pieces

## CATALOG NUMBER

**20817-874**



Suitable for insertion and extraction forces up to 1500 N (per pair). Robust board fixing via double bolts. The insertion function will be supported by a keying part which will be assembled onto the horizontal rail.

## CERTIFICATIONS



## FEATURES

Suitable for insertion and extraction forces up to 1500 N (per pair)

Handle in PA, fiberglass reinforced, UL 94V 0

Robust board fixing with double bolt fixing

Microswitches can be fitted

Symmetrical, identical handle at top/bottom

## PRODUCT ATTRIBUTES

Product Type: Handle

Type: Inserter/Extractor

Works With: Front Panels

Handle Type: XL

Width: 20.1mm

Material: Zinc Alloy; Polyamide

Color: Jet Black

Flammability Rating: UL® 94V-0

Package Quantity: 10

Color Code: RAL 9005

Depth: 42.39mm

Gross Weight: 0.374kg

Height: 73.57mm

## ADDITIONAL PRODUCT DETAILS

Please order front panels separately and Micro switch.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**