


# Outdoor Unibody Cabinet

## Data Solutions



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

## CERTIFICATIONS



## FEATURES

Double-walled, Al

IP 55

One-piece inner case with removable outer cladding

Heat dissipation through natural convection, max. 5 W/K (11249-003) / 6 W/K (11249-005)

## SPECIFICATIONS

**Material:** Aluminum

Table 1/3

| Catalog Number | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|----------------|-----------------|----------------|-------------|--------|-------|-------|
| 11249-005      | Outdoor Cabinet | Unibody        | 20U         | 1100mm | 700mm | 500mm |

| CatalogNumber | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|---------------|-----------------|----------------|-------------|--------|-------|-------|
| 11249-003     | Outdoor Cabinet | Unibody        | 16U         | 930mm  | 700mm | 500mm |

Table 2/3

| Catalog Number | Wall Type     | Door Type   | Access | Cooling            | EMC Shielding | Complies With                                                                                     |
|----------------|---------------|-------------|--------|--------------------|---------------|---------------------------------------------------------------------------------------------------|
| 11249-005      | Double Walled | Single Door | Front  | Natural Convection | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 11249-003      | Double Walled | Single Door | Front  | Natural Convection | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |

Table 3/3

| Catalog Number | Package Quantity | Finish        |
|----------------|------------------|---------------|
| 11249-005      | 1                | Powder Coated |
| 11249-003      | 1                | Powder Coated |

## ADDITIONAL PRODUCT DETAILS

Please order panel/slide mounts separately.

Further base/plinth heights on request.

Please order wall-mounting assembly kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**