

Insulated Tape Conductor



FEATURES

Provides a path to ground for lightning currents

Available in various colors to match building or design requirements

SPECIFICATIONS

Insulation Thickness: 1.0 - 1.5 mm

Table 1/2

Catalog Number	Article Number	Material	Conductor Width	Conductor Thickness	Length	Color
ATGY25350	710770	Aluminum, Polyvinylchloride	25 mm	3 mm	50m	Gray
ATWH25350	710790	Aluminum, Polyvinylchloride	25 mm	3 mm	50m	White
CTBL25325	710595	Copper, Polyvinylchloride	25 mm	3 mm	25m	Black
CTBN25325	710605	Copper, Polyvinylchloride	25 mm	3 mm	25m	Brown
CTGN25325	710616	Copper, Polyvinylchloride	25 mm	3 mm	25m	Green

CatalogNumber	Article Number	Material	Conductor Width	Conductor Thickness	Length	Color
CTGN25630	710620	Copper, Polyvinylchloride	25 mm	6 mm	30m	Green
CTGY25325	710645	Copper, Polyvinylchloride	25 mm	3 mm	25m	Gray
CTST25325	710655	Copper, Polyvinylchloride	25 mm	3 mm	25m	Stone
CTWH25325	710666	Copper, Polyvinylchloride	25 mm	3 mm	25m	White
CTYGN25325	710667	Copper, Polyvinylchloride	25 mm	3 mm	25m	Green, Yellow

Table 2/2

Catalog Number	Article Number	Unit Weight
ATGY25350	710770	0.3 kg
ATWH25350	710790	0.3 kg
CTBL25325	710595	0.77 kg
CTBN25325	710605	0.77 kg
CTGN25325	710616	0.77 kg
CTGN25630	710620	1.55 kg
CTGY25325	710645	0.77 kg
CTST25325	710655	0.77 kg
CTWH25325	710666	0.77 kg
CTYGN25325	710667	0.77 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE