


# Combined Mounting Kit for Chassis

## Servicios públicos de energía



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

### CERTIFICACIONES



### CARACTERÍSTICAS

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Package Quantity | Rack Width 1 | Rack Width 2 | Product Family | Product Type | Rack Height |
|--------------------|------------------|--------------|--------------|----------------|--------------|-------------|
| 24562-484          | 1                | 84 HP        |              | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-420          | 1                | 20 HP        | 62 HP        | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-440          | 1                | 40 HP        | 42 HP        | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-442          | 1                | 42 HP        | 40 HP        | EuropacPRO     | Mounting Kit | 6 U         |

| Número de catálogo | Package Quantity | Rack Width 1 | Rack Width 2 | Product Family | Product Type | Rack Height |
|--------------------|------------------|--------------|--------------|----------------|--------------|-------------|
| 24562-463          | 1                | 63 HP        | 19 HP        | EuropacPRO     | Mounting Kit | 6 U         |

Table 2/2

| Número de catálogo | Tipo     | Works With |
|--------------------|----------|------------|
| 24562-484          | Combined | Subracks   |
| 24562-420          | Combined | Subracks   |
| 24562-440          | Combined | Subracks   |
| 24562-442          | Combined | Subracks   |
| 24562-463          | Combined | Subracks   |

## ADDITIONAL PRODUCT DETAILS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**