

QTVR Self-Regulating Heating Cable



nVent RAYCHEM QTVR self-regulating trace heating cables are suitable for freeze protection of large pipes/vessels with high heat loss, and for process temperature maintenance applications without steam-cleaning requirements, up to 225 °F/110 °C. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

CARACTERÍSTICAS

Simplified design for hazardous areas: unconditional T4 class

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

ESPECIFICACIONES

Max Maintain or Continuous Exposure Temperature, Power On/Off:	110 °C
Max Intermittent Exposure Temperature, Power On/Off:	110 °C
Ground Path Type:	Trenzado
Outer Jacket Material:	Fluoropolímero
Area Classification:	Non-Hazardous; Hazardous

Table 1/1

Número de catálogo	Nombre del artículo	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
040615-000	15QTVR2-CT	200 – 277 V	51 W/m	
148345-000	15QTVR1-CT	100 – 130 V		52 W/m
259951-000	10QTVR1-CT	100 – 130 V		39 W/m
391991-000	10QTVR2-CT	200 – 277 V	38 W/m	

Número de catálogo	Nombre del artículo	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 120V
498703-000	20QTVR1-CT	100 – 130 V		66 W/m
988967-000	20QTVR2-CT	200 – 277 V	64 W/m	

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT