

# EuropacPRO Adapter for Rear Fixing, DL3 Standard



Adapter for rear fixing of a subrack in accordance with DL3 standard into a cabinet. It guarantees shock and vibration resistance up to 25 g.

## CERTIFICATIONS



## FEATURES

Guarantees vibration resistance up to 25g as per IEC 61587 DL3

Adapters for other cabinet models available on request

Mounts onto rear of ruggedized subrack and to Varistar cabinet uprights

## SPECIFICATIONS

|                        |            |
|------------------------|------------|
| <b>Product Type:</b>   | Adapter    |
| <b>Product Family:</b> | EuropacPRO |
| <b>Works With:</b>     | Subracks   |

Table 1/1

| Catalog Number | Rack Height | Package Quantity | Finish                         | Material        | Quick Ship |
|----------------|-------------|------------------|--------------------------------|-----------------|------------|
| 24568-198      | 3U          | 2                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |
| 24568-498      | 6U          | 4                | Aluminum-Zinc Plated, Anodized | Steel, Aluminum | No         |

ADDITIONAL PRODUCT DETAILS

Adapter cannot be used together with corner profile.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE