

Fast Fuel Sensor Probe with Leader Cable, No Connector



nVent RAYCHEM TraceTek TT-FFS-100 is a range of fast response sensing probes, with 100 mm and 250 mm active length, to detect hydrocarbon fuel floating on water or spreading on a flat surface. Supplied with leader cable that has pigtail lead but no connector.

CARACTERÍSTICAS

Simple and fast to install: small, lightweight

Fast response : Reaction time is typically a few seconds, for light or middle weight fuels such as gasoline, jet fuel, and diesel

Detects crude oil and some heavier weight fuels and heating oils: but becomes progressively slower as the fuel volatility decreases

Self reset: in many cases the sensor probe will reset after it is removed from the spill and the fuel is allowed to evaporate; some heavier fuels require the sensor to be soaked in isopropyl alcohol or naphtha in order to clear the residuals

Increases safety: of back-up diesel generators, reducing the risk of fire if a leak were to occur

FM approved: meets the 7745 Approval Standard for Diesel Leak Detectors for detecting diesel fuel leaks in commercial buildings

ESPECIFICACIONES

Model:	Fast Fuel Sensor
Detection:	Combustible
Detection Method:	Raychem Conductive-Polymer Technology
Temperatura de funcionamiento:	-40 a 85 °C

Table 1/1

Número de catálogo	Nombre del artículo	Suitable for Outdoor Installation
P000000984	TT-FFS-100-L-1	No

Número de catálogo	Nombre del artículo	Suitable for Outdoor Installation
P000002289	TT-FFS-WR-250-L-10	Sí
P000000986	TT-FFS-100-L-10	No
P000000989	TT-FFS-250-L-10	No
P000000988	TT-FFS-250-L-3	No
P000000987	TT-FFS-250-L-1	No
P000000985	TT-FFS-100-L-3	No
P000002304	TT-FFS-WR-100-L-10	Sí

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT