

Hazardous Area Control Panel



nVent RAYCHEM multi-circuit heat trace control panels are designed, manufactured, tested and certified in-house. This brings design flexibility and assured quality. Based on nVent HOFFMAN stainless steel enclosures, they are configured with RAYCHEM heat trace controllers, solid-state relays and a user interface. Circuit ratings go up to 63 Amps / 690 Vac. The entire panel is ATEX/IECEx certified for Zone 2 hazardous area, is weatherproof and can be winterized to -60°C. Seamless integration with existing RAYCHEM control systems and optional wireless connectivity can reduce overall cost of ownership.

CARACTERÍSTICAS

Reduced total installation cost through optimal C&M architecture by space savings in substation, reduced cabling infrastructure, lower panel cost versus traditional Zone-1 (Ex-d) panels and higher loads (63A) leading to longer circuits and flexibility in design

Quality assured and faster delivery due to In-house design, manufacturing, quality control, logistics and In-house certification

Operational efficiency and reduced total operating cost by easier field monitoring (via touch screen), easier access inside panel (versus Zone 1 panel).

ESPECIFICACIONES

Table 1/2

Número de catálogo	Nombre del artículo	Material	Area Classification	Clasificación IP	Controller Type	Voltage Rating
PNLZN2	PNLZN2	Stainless Steel 316	Zone 2	IP66	NGC-40, NGC-30, Elexant 4020i	240 V

Table 2/2

Número de catálogo	Nombre del artículo	Temperatura de funcionamiento	Temperatura de almacenamiento
PNLZN2	PNLZN2	-40 to 60 °C	-40 to 75 °C

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de

atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT