

Internal side panels | Potencia y Distribución, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

CARACTERÍSTICAS

Descripción: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Suministro: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

ESPECIFICACIONES

Espesor: 1.5mm
Acabado: Galvanizado
Material: Acero

Table 1/1						
Número de catálogo	Altura	Anchura	Fondo	Tamaño del panel	Material del armario	Familia de productos
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Acero suave	Libre-permanente
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Acero suave	Libre-permanente
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Acero suave	Libre-permanente
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Acero suave	Libre-permanente
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Acero suave	Libre-permanente
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Acero suave	Libre-permanente
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Acero suave	Libre-permanente
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Acero suave	Libre-permanente
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Acero suave	Libre-permanente
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Acero suave	Libre-permanente
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Acero suave	Libre-permanente
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Acero suave	Libre-permanente
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Acero suave	Libre-permanente
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Acero suave	Libre-permanente
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Acero suave	Libre-permanente
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Acero suave	Libre-permanente

Número de catálogo	Altura	Anchura	Fondo	Tamaño del panel	Material del armario	Familia de productos
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Acero suave	Libre-permanente
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Acero suave	Libre-permanente

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE