

Guide Rail With Coding for CompactPCI/VME64x, PC

Servicios públicos de energía

New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CARACTERÍSTICAS

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

ESPECIFICACIONES

Table 1/2

Número de catálogo	Material	Color	Package Quantity	Board Depth	Groove Width	Cumple con
24568-356	Polycarbonato	Rojo		160 mm	2	EN 45545-2
24568-357	Polycarbonato	Rojo		70 mm	2	EN 45545-2
24568-358	Polycarbonato	Gris		160 mm	2	EN 45545-2

Número de catálogo	Material	Color	Package Quantity	Board Depth	Groove Width	Cumple con
24568-360	Polycarbonato	Gris		70 mm	2	EN 45545-2
64568-085	Polycarbonato	Rojo	50	70 mm	2	EN 45545-2
64568-086	Polycarbonato	Gris	50	70 mm	2	EN 45545-2
64568-089	Polycarbonato	Rojo	50	160 mm	2	EN 45545-2
64568-090	Polycarbonato	Gris	50	160 mm	2	EN 45545-2
64568-091	Polycarbonato	Rojo	50	220 mm	2	EN 45545-2
64568-092	Polycarbonato	Gris	50	220 mm	2	EN 45545-2
24568-331	Polycarbonate, Aluminum	Red, Silver	10	280 mm	2.5	EN 45545-2
24568-332	Polycarbonate, Aluminum	Red, Silver	10	340 mm	2.5	EN 45545-2
24568-341	Polycarbonate, Aluminum	Grey, Silver	10	280 mm	2.5	EN 45545-2
24568-342	Polycarbonate, Aluminum	Grey, Silver	10	340 mm	2.5	EN 45545-2
64568-111	Polycarbonate, Aluminum	Red, Silver	50	220 mm	2.5	EN 45545-2
64568-112	Polycarbonate, Aluminum	Grey, Silver	50	220 mm	2.5	EN 45545-2
64568-110	Polycarbonate, Aluminum	Grey, Silver	50	160 mm	2.5	EN 45545-2
64568-109	Polycarbonate, Aluminum	Red, Silver	50	160 mm	2.5	EN 45545-2

Table 2/2

Número de catálogo	Product Family	Product Type	Tipo	Works With
--------------------	----------------	--------------	------	------------

24568-356	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-357	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-358	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-360	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-085	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-086	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-089	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-090	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

64568-091	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-092	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-331	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-332	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-341	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
24568-342	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-111	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-112	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

64568-110	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems
64568-109	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding	Subracks, Cases, 19" Chassis, Systems

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE