

Outdoor Modular VENT Cabinet

Servicios públicos de energía



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

CERTIFICACIONES



CARACTERÍSTICAS

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from all sides

ESPECIFICACIONES

Table 1/2

Número de catálogo	Product Type	Product Family	Rack Height	Altura	Ancho	Profundidad
10149-337	Outdoor Cabinet	Modular	29 U	1530 mm	1300 mm	630 mm
10149-334	Outdoor Cabinet	Modular	29 U	1530 mm	700 mm	730 mm

Número de catálogo	Product Type	Product Family	Rack Height	Altura	Ancho	Profundidad
10149-336	Outdoor Cabinet	Modular	29 U	1530 mm	1300 mm	630 mm

Table 2/2

Número de catálogo	Wall Type	Door Type	Acceso	Refrigeración	EMC Shielding	Cumple con
10149-337	Double Walled	Double Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4
10149-334	Double Walled	Single Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4
10149-336	Double Walled	Double Door	Front	Fan Ventilation	No (Retrofittable)	IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4, RC2

ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

qW = specific heat dissipation capacity according to ETSI EN 300 019-1-4.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte