

BSA Self-Regulating Heating Cable



nVent RAYCHEM BSA self-regulating trace heating cables are an ideal solution for freeze protection of pipes and vessels and for process temperature maintenance, in non-hazardous industrial locations, without steam-cleaning requirement. They maintain process temperatures up to 65°C and can withstand intermittent exposure temperatures up to 85°C. BSA heating cables use the same heating core and polyolefin inner jacket as the BTV. The earth path consists of an aluminum foil wrap and metallic drain wires, providing 100% electrical protection coverage. The polyolefin outer jacket is suitable for mild inorganic solutions and provides excellent protection.

CARACTERÍSTICAS

Foil wrap /drain-wire construction and modified polyolefin jackets provide a highly flexible cable

The unique construction allows stripping the jackets in no time, for fast connection

100% electrical earth path coverage for ultimate safety

Reliable long life performance with a 10 year product warranty available

ESPECIFICACIONES

Supply Voltage:	0 – 230 V
Ground Path Type:	Foil and Drainwire
Material conductor:	Nickel-Plated Copper
Area Classification:	Non-Hazardous
Outer Jacket Material:	Poliiolefina

Table 1/1

Número de catálogo	Nombre del artículo	Nominal Power Output @ 10°C, 230V	Max Circuit Length	Nominal Width	Nominal Thickness
P000002271	3BSA2-DR	10 W/m	150 m	13.7 mm	6.2 mm
P000002272	7BSA2-DR	23 W/m	120 m	13.7 mm	6.2 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT