

Cable Entry Gland Plate Round Modular, CCFR



A fast, safe and versatile modular cable entry system in a round configuration, providing secure seals and strain relief for pre-assembled and unassembled cables with or without connectors.

ESTÁNDARES DEL SECTOR

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

CARACTERÍSTICAS

0

Halogen and silicone free cable entry system

The frames, inlays and grommets can be combined in many ways ensuring you many versatile configuration options

No need to disassemble and reconnect connectors on cables so manufactures warranty is not voided

CCFR cable entry is quick and easy to assemble

It is made of a sturdy, glass-fiber reinforced plastic

CCFG grommets needs to be ordered separately

CCFD dividers are bought separately as needed

Operating Temperature: -40 to 120 °C / -40 to 248 °F

Note: CCFR63 is presently awaiting UL review for addition to file; order components separately if UL requirement is present

ESPECIFICACIONES

Table 1/1						
Número de catálogo	Número de artículo	Tamaño de mecanizado	Altura	Anchura	Fondo	Material
CCFR20	59525	21.6mm	48mm	48mm	35mm	Elastómero termoplástico
CCFR25	59526	26.6mm	48mm	48mm	35mm	Elastómero termoplástico
CCFR32	59527	33.6mm	48mm	48mm	35mm	Elastómero termoplástico
CCFR40	59528	40.4mm	80mm	80mm	35mm	Elastómero termoplástico
CCFR50	59529	50.4mm	80mm	80mm	35mm	Elastómero termoplástico
CCFR63	59532	63.4mm	80mm	80mm	35mm	Elastómero termoplástico

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.