


# Low-Profile Splice Kit



nVent RAYCHEM S-150 is a cold-applied low profile splice for trace heating cables in both non-hazardous and hazardous locations. Includes cold-applied heating cable core sealer.

## CARACTERÍSTICAS

Simple and fast to install and test

Cold-applied: no heat gun or hot work permit required, re-enterable

High performance: resistant to impact, high temperature, chemicals and UV

Reliable during long life: 10 year product warranty available, maintenance free

## ESPECIFICACIONES

Table 1/2

| Número de catálogo | Nombre del artículo | Model                       | Tipo de conexión | Voltage Rating for FM, CSA | Voltage Rating for PTB | Current Rating for FM, CSA |
|--------------------|---------------------|-----------------------------|------------------|----------------------------|------------------------|----------------------------|
| 497537-000         | S-150               | Heating Cable/Heating Cable | Cold Applied     | 277 V                      | 254 V                  | 50 A                       |

Table 2/2

| Número de catálogo | Nombre del artículo | Current Rating for PTB | Max Exposure Temperature | Below Insulation |
|--------------------|---------------------|------------------------|--------------------------|------------------|
| 497537-000         | S-150               | 40 A                   | 215 °C                   | Sí               |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la

propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

**Norteamérica**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latinoamérica**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**