


Guide Rail With DIN Connector Fixing

Power Utilities



The the standard type guide rail with connector fixing allows the user to clip the DIN connectors directly onto the guide rails. Only applicable with Euroboards with the dimensions 100 x 160 mm and 100 x 220 mm. Suitable for RatiopacPRO/-AIR, PropacPRO, CompacPRO and EuropacPRO.

CERTIFICACIONES



CARACTERÍSTICAS

Easy and economic mounting of connectors through snap connections as alternative to z-rails or horizontal rails with integrated z-rail

For single Euroboard format 100 × 160 mm or 100 × 220 mm; not suitable for double Euroboard format

Plastic guide rail, one piece, red, for 2 mm groove width

Can be clipped into horizontal rails in Al extrusion

Can be clipped into 1.5 mm thick plate

Storage temperature: from -40 °C ... 130 °C

ESPECIFICACIONES

Table 1/2

Número de catálogo	Cantidad del paquete	Profundidad de la placa	Ancho de ranura	Color	Material	Familia de productos
--------------------	----------------------	-------------------------	-----------------	-------	----------	----------------------

64560-075	1	220 mm	2	Rojo	De plástico	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac
64560-074	1	160 mm	2	Rojo	De plástico	EuropacPRO, RatiopacPRO, RatiopacPRO AIRE, CompacPRO, PropacPRO, MultipacPRO, InPac

Table 2/2

Número de catálogo	Tipo de producto	Tipo	Compatible con	Unidad de paquete
64560-075	Guía de tren	Estándar con conector DIN	Subpistas, Casos, Chasis	Par
64560-074	Guía de tren	Estándar con conector DIN	Subpistas, Casos, Chasis	Par

DETALLES ADICIONALES DEL PRODUCTO

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestra poderosa cartera de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE