

Varistar CP Swing Frame for 800 mm Width

Servicios públicos de energía

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

CARACTERÍSTICAS

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Height	Color	Color Code	Altura	Material	Product Type
21630-669	24 U	Black Grey	RAL 7021	1200 mm	Acero	Cabinet/Rack Frame
21630-680	24 U	Black Grey	RAL 7021	1200 mm	Acero	Cabinet/Rack Frame
21630-671	29 U	Black Grey	RAL 7021	1400 mm	Acero	Cabinet/Rack Frame
21630-681	29 U	Black Grey	RAL 7021	1400 mm	Acero	Cabinet/Rack Frame
21630-673	33 U	Black Grey	RAL 7021	1600 mm	Acero	Cabinet/Rack Frame
21630-682	33 U	Black Grey	RAL 7021	1600 mm	Acero	Cabinet/Rack Frame
21630-675	38 U	Black Grey	RAL 7021	1800 mm	Acero	Cabinet/Rack Frame

Número de catálogo	Rack Height	Color	Color Code	Altura	Material	Product Type
21630-683	38 U	Black Grey	RAL 7021	1800 mm	Acero	Cabinet/Rack Frame
21630-677	42 U	Black Grey	RAL 7021	2000 mm	Acero	Cabinet/Rack Frame
21630-684	42 U	Black Grey	RAL 7021	2000 mm	Acero	Cabinet/Rack Frame
21630-679	47 U	Black Grey	RAL 7021	2200 mm	Acero	Cabinet/Rack Frame
21630-685	47 U	Black Grey	RAL 7021	2200 mm	Acero	Cabinet/Rack Frame

Table 2/2

Número de catálogo	Protection Rating	Ancho
21630-669	IP20	800 mm
21630-680	IP20	800 mm
21630-671	IP20	800 mm
21630-681	IP20	800 mm
21630-673	IP20	800 mm
21630-682	IP20	800 mm
21630-675	IP20	800 mm
21630-683	IP20	800 mm
21630-677	IP20	800 mm
21630-684	IP20	800 mm
21630-679	IP20	800 mm
21630-685	IP20	800 mm

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE