

LSZH Coated Saddle Clip

nVent PYROTENAX LSZH Coated Saddle Clip is a range of low smoke zero halogen (LSZH) coated copper fixing saddles for mineral insulated (MI) cables. Available in various sizes and colors. For fixing LSZH covered light or heavy duty MI cables.

FEATURES

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Table 1/1

Catalog Number	Tube/Cable Diameter	Color
RSFL272BK	6.8 mm	Black
RSFL272OR	6.8 mm	Orange
RSFL272RD	6.8 mm	Red
RSFL272WH	6.8 mm	White
RSFL302BK	7.6 mm	Black
RSFL302OR	7.6 mm	Orange
RSFL302RD	7.6 mm	Red
RSFL302WH	7.6 mm	White
RSFL342BK	8.6 mm	Black
RSFL342OR	8.6 mm	Orange

Catalog Number	Tube/Cable Diameter	Color
RSFL342RD	8.6 mm	Red
RSFL342WH	8.6 mm	White
RSFL382BK	9.6 mm	Black
RSFL382OR	9.6 mm	Orange
RSFL382RD	9.6 mm	Red
RSFL382WH	9.6 mm	White
RSFL422BK	10.6 mm	Black
RSFL422OR	10.6 mm	Orange
RSFL422RD	10.6 mm	Red
RSFL422WH	10.6 mm	White
RSFL462BK	11.6 mm	Black
RSFL462OR	11.6 mm	Orange
RSFL462RD	11.6 mm	Red
RSFL462WH	11.6 mm	White
RSFL502BK	12.4 mm	Black
RSFL502OR	12.4 mm	Orange
RSFL502RD	12.4 mm	Red
RSFL502WH	12.4 mm	White

Catalog Number	Tube/Cable Diameter	Color
RSFL542BK	13.4 mm	Black
RSFL542OR	13.4 mm	Orange
RSFL542RD	13.4 mm	Red
RSFL542WH	13.4 mm	White
RSFL592BK	14.4 mm	Black
RSFL592OR	14.4 mm	Orange
RSFL592RD	14.4 mm	Red
RSFL592WH	14.4 mm	White
RSFL632BK	15.4 mm	Black
RSFL632OR	15.4 mm	Orange
RSFL632RD	15.4 mm	Red
RSFL632WH	15.4 mm	White
RSFL702BK	17.3 mm	Black
RSFL702OR	17.3 mm	Orange
RSFL702RD	17.3 mm	Red
RSFL702WH	17.3 mm	White
RSFL752BK	18.3 mm	Black
RSFL752OR	18.3 mm	Orange

Catalog Number	Tube/Cable Diameter	Color
RSFL752RD	18.3 mm	Red
RSFL752WH	18.3 mm	White
RSFL812OR	20.2 mm	Orange
RSFL812WH	20.2 mm	White
RSFL932OR	22.7 mm	Orange
RSFL932RD	22.7 mm	Red
RSFL932WH	22.7 mm	White

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT