

# Z-Rail for Connector, EN 60603-2, DIN 41612

## Servicios públicos de energía



Z-rail for connector in accordance with EN 60603-2 (DIN 41612).

### CERTIFICACIONES



### CARACTERÍSTICAS

Z-rails are bolted to the subrack for connector mounting (rear horizontal rail type ST, threaded insert inserted)

For connectors to EN 60603-2 (DIN 41612)

Aluminum extrusion, anodized

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Rack Width | Package Quantity | Longitud  | Product Family                                                                | Product Type | Works With         |
|--------------------|------------|------------------|-----------|-------------------------------------------------------------------------------|--------------|--------------------|
| 30822-089          | 84 HP      | 1                | 426.72 mm | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO | Z-Rail       | Subracks,<br>Cases |

| Número de catálogo | Rack Width | Package Quantity | Longitud  | Product Family                                                 | Product Type | Works With      |
|--------------------|------------|------------------|-----------|----------------------------------------------------------------|--------------|-----------------|
| 30822-033          | 28 HP      | 1                | 142.24 mm | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-047          | 42 HP      | 1                | 213.36 mm | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-065          | 60 HP      | 1                | 304.8 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-166          | 4 HP       | 1                | 20.32 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-170          | 8 HP       | 1                | 40.64 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |

Table 2/2

| Número de catálogo | Certificaciones |
|--------------------|-----------------|
| 30822-089          | RoHS            |
| 30822-033          | RoHS            |
| 30822-047          | RoHS            |
| 30822-065          | RoHS            |
| 30822-166          | RoHS            |

| Número de catálogo | Certificaciones |
|--------------------|-----------------|
| 30822-170          |                 |

## ADDITIONAL PRODUCT DETAILS

For attaching the z-rail to the horizontal rail a threaded insert and Torx panhead screw are required; please order these separately.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**