


Horizontal Pouring Basin, Side Fill, 45°, Right Hand



Angular side fill horizontal pouring basins are used when interferences of the structure will not allow top filling of the sleeve and the interferences are directly next to the tap hole in the sleeve.

CARACTERÍSTICAS

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal side fill sleeves

ESPECIFICACIONES

Material: Grafito

Table 1/2

Número de catálogo	Diámetro (Ø)	Longitud 1 (L1)	Longitud 2 (L2)	Anchura (W)	Altura 1 (H1)	Altura 2 (H2)
RBWS2620RHF	64 mm	141 mm	83 mm	76 mm	154mm	76mm
RBWS2620RHM	95 mm	141 mm	83 mm	76 mm	154mm	76mm
RBWS2620RHJ	76 mm	141 mm	83 mm	76 mm	154mm	76mm

Table 2/2

Número de catálogo	Ángulo (a)
RBWS2620RHF	45 °

Número de catálogo	Ángulo (a)
RBWS2620RHM	45 °
RBWS2620RHJ	45 °


DETALLES ADICIONALES DEL PRODUCTO

RBWS2620 pouring basins require one RBW350 and one RBW664 pouring basin frame and one RBS5000 bolt retainer (sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMAS



ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

+1.800.753.9221

Opción 1: Atención al
cliente

Opción 2: Soporte técnico

Europa

Países Bajos:

+31 800-0200135

Francia:

+33 800 901 793

Europa

Alemania:

800 1890272

Otros países:

+31 13 5835404

Asia-Pacífico

Shanghái:

+86 21 2412 1618/19

Sídney:

+61 2 9751 8500



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

©2025 nVent. Todas las marcas y logotipos de nVent son propiedad de nVent Services GmbH o sus filiales, o se utilizan bajo su licencia. El resto de las marcas comerciales son propiedad de sus respectivos propietarios. nVent se reserva el derecho a cambiar las especificaciones sin previo aviso.

Este documento lo ha generado el sistema.